

Hyramic


Hybrid Ceramics for Dental CAD/CAM & Chairside System



• RELIABLE MATERIALS EXPERT •


Hyramic

- Elastic Modulus Approximates to Natural Dentin
- Simple Milling, No Need Sintering
- Chairside Instant Restoration




STRENGTH
180MPa

• Indications




- Available for Single & Multilayer Shades


HT 18-14-12



LT 18-14-12



ML 18-14-12



• Chemical Compositions

Resin polymers	13%-43%
Inorganic filler	55%-85%
Additive	<1%
Colorant	<1%

• Technical Parameters

Flexural strength	≥180MPa
Water absorption	≤25μg/cm ³
Solubility in water	≤2μg/cm ³

Shenzhen Upcera Dental Technology CO., Ltd.

Tel: +86-755-8882-0818 E-mail: sales@upcera.com

www.upcera-dental.com

Follow us on >>

